



General ordering data

Order No.	0170320000
Part designation	SAKG 28 II
Version	Special terminal, special connections, 35 mm ² , Screw connection, KrG, Medium yellow, TS 32
EAN	4008190126247
Qty.	10 pc(s).

Product notes

Note, technical data	Conductor connection with cable lugs according to DIN 46234 and DIN 46235, from 6 .. 50 mm ²
----------------------	---

Additional technical data

Colour of insulating material	Medium yellow
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 32
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	Open
Operating temperature range	- 60 °C, + 130 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Stud terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	110 A
Min. cross-section (CSA)	AWG 6
Max. cross-section (CSA)	AWG 1

Conductors for clamping (rated connection)

Clamping range, min.	6 mm ²
----------------------	-------------------

Conductors for clamping (rated connection)

Clamping range, max.	50 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	1
Clamping screw	M 6
Tightening torque range	3.0...6.0 Nm
AWG conductor size, min.	AWG 6
AWG conductor size, max.	AWG 1
AWG conductor size, min.	13.3 mm ²
AWG conductor size, max.	42.41 mm ²

Dimensions

Width	28 mm
Height of lowest version	53 mm
Length	70 mm
Weight	100.5 g
TS 32 offset	35 mm

Rating data

Rated cross-section	35 mm ²
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Rated current	125 A
Standards	IEC 60947-7-1
Current with max. conductor	150 A
Pollution severity	3

UL rating data

Voltage (UL)	600 V
Current (UL)	115 A
Min. cross-section (UL)	AWG 8
Max. cross-section (UL)	AWG 2

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000897
ETIM 3.0	EC000897
eClass 4.1	27-14-11-31
eClass 5.0	27-14-11-31
eClass 5.1	27-14-11-31

Similar products

Order No.	Part designation	Version
0170020000	SAKG 28 I	Special terminal, special connections, 35 mm ² , Screw connection, KrG, Medium yellow, TS 32
0185020000	SAKG 28 II/GW	Special terminal, special connections, 35 mm ² , Screw connection, KrG, Medium yellow, TS 32
0170820000	SAKG 28 III	Special terminal, special connections, 35 mm ² , Screw connection, KrG, Medium yellow, TS 32