

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0887283400](#)
Status: **Active**
Overview: USB
Description: Universal Serial Bus (USB) Shielded I/O Cable Assembly: A-to-Pigtail Full-Rated, 2.08m (6.82') Length

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	88740
Comments	Full-rated
Connector to Connector	USB Type A-to-Pigtail
Overview	<u>USB</u>
Product Name	USB

Physical

Cable Length	2.08m (6.82')
Circuits (Loaded)	4
Gender	Male
Lock to Mating Part	Yes
Packaging Type	Bag
Pitch - Mating Interface (in)	0.079 In, 0.098 In
Pitch - Mating Interface (mm)	2.00 mm, 2.50 mm
Single Ended	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round


Electrical

Current - Maximum	1A
Shielded	Yes

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-88738-001
---------------	--------------



EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
 Not Reviewed
**Halogen-Free
Status**

China RoHS



Not Reviewed

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[88740Series](#)

Mates With

Universal Serial Bus (USB) Type A
 Receptacle [67329](#) , [67230](#) , [89485](#)