

Search Results

Evaluate
 - FAQ's
 - Line Cards
 - PDF-Copper Cabli ..

Design a Solution
 - Specification Sheets
 - PDF-TX5500 Categ ..

How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'PFP5504RD-UY'

Your search criteria matched only one product, shown below

PFP5504RD-UY



- Exceeds requirements of ANSI/TIA-568-C.2 Category 5e and ISO 11801 2nd Edition Class D channel standards
- Exceeds requirements of ANSI/TIA-568-C.2 Category 5e and IEC 61156-5 Category 5e component standards
- Meets requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Cable diameter: 0.235 in. (5.97mm) nominal
- Installation temperature range: 32°F to 122°F (0°C to 50°C)
- Operating temperature range: -4°F to 140°F (-20°C to 60°C)
- Descending length cable markings enable easy identification of remaining cable which reduces installation time and cable scrap
- **Available in North America only**

• Part Number	PFP5504RD-UY
• RoHS Compliance Status	Compliant
• Part Description	Category 5e, plenum (CMP), 4-pair, F/UTP copper cable. Copper conductors are 24 AWG construction with FEP insulation. Conductors are twisted in pairs, surrounded by an overall polyester aluminum foil with stranded copper drain wire and protected by a low smoke flame-retardant PVC jacket.
• Product Type	Copper Cable
• BMEcat - Cable color	Red
• Cable Color	Red
• Cable Type	F/UTP
• Flammability Rating	CMP
• Pricing Description	Copper Cable, Cat 5e, 4-PR, 24 AWG, F/UTP, CMP, Red, 1000 Feet/305m
• Min. Order UOM	FT
• Min. Order Qty.	5000
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.