

USB 2.0 Cable with 5A Rating, USB-C to USB-C (M/M), 6 ft.

MODEL NUMBER: **U040-006-C-5A**



Description

The U040-006-C-5A USB 2.0 Hi-Speed Cable (M/M) carries a 5A power rating and supports a full 100W of power, which is plenty for fast-charging large-capacity mobile devices, such as the Apple® MacBook Pro. It connects any two devices with USB-C ports, such as smartphones, tablets, computers and wall chargers.

This six-foot cable also supports USB 2.0 data transfer speeds up to 480 Mbps. Reversible USB-C male connectors plug into a USB port in either direction for fast, fumble-free connection every time.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded nickel-plated connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. The U040-006-C-5A is backward compatible with previous USB generations.

USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

Features

Connects 2 USB-C Devices

- Power output up to 20V 5A (100W) for fast-charging large mobile devices, such as MacBook Pro
- Recommended for connecting smartphones, tablets, computers, wall chargers and other USB-C devices
- Supports USB 2.0 data transfer speeds up to 480 Mbps
- Backward compatible with previous USB generations

Highlights

- Power output up to 5A for fast-charging large mobile devices
- Supports data transfer speeds up to 480 Mbps
- Reversible USB-C plugs on both ends for fumble-free connection
- Integral strain relief protects against stress and cracking
- Backward compatible with previous USB generations

System Requirements

- Devices with USB-C female connectors

Package Includes

- USB 2.0 Hi-Speed Cable with 5A Rating, USB-C to USB-C (M/M), 6 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Reversible USB-C Male Connectors

- Fumble-free reversible plugs connect in either direction to ensure fast, easy connection every time

Premium Construction

- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss
- Foil and braid shielding delivers reliable, error-free signal quality and EMI/RFI protection

Specifications

MODEL TEXT	
What Does This Product Do?	USB-C cable provides up to 20V 5A (100W) of power—more than enough to charge large-capacity mobile devices, such as the MacBook Pro®. Also connects smartphones, computers, wall chargers and other USB-C devices.
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Cable Length (cm)	182.9
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.500 x 7.000 x 9.000
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.3000
Shipping Weight (kg)	0.14
Material of Construction	PVC
Color	Black
Cable Outer Diameter (OD)	4.0MM
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Operating Humidity Range	10% to 85%
Storage Humidity Range	5% to 90%
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
CERTIFICATIONS	
Certifications	Tested to: CE, ROHS
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>