

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [43335-1002](#)
Status: **Active**
Overview: [Flat Blade](#)
Description: 7.50mm Pitch, Flat Blade Appliance Receptacle Housing, Single Row, 2 Circuits, Nylon PA66, UL 94V-2, Black with TPA

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PSX-43335-9999 \(PDF\)](#)
[Packaging Specification PK-43335-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [43335](#)
Application Power, Wire-to-Wire
Comments Glow Wire Equivalent Part Number [433352002](#)
Overview [Flat Blade](#)
Product Name Flat Blade
UPC 800753851108

Physical

Breakaway No
Circuits (maximum) 2
Color - Resin Natural
Flammability 94V-2
Gender Receptacle
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 1.651/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 7.50mm
Pitch - Termination Interface 7.50mm
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -40°C to +75°C

Material Info

Reference - Drawing Numbers

Packaging Specification PK-43335-001
Product Specification PSX-43335-9999
Sales Drawing SD-43335-*002




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[43335Series](#)

Mates With

[43180](#) Flat Blade Plug Housing

Use With

[43375](#) Female Terminals