

PANEL MOUNT INDICATOR, NON-RELAMPABLE

NEON AND INCANDESCENT TECHNOLOGY

MOUNTING HOLE, Ø 0.310"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
NEON 115VAC SERIES				
WL-2150A1	RED	105-125VAC	1.5mA	25,000
WL-2150A2	CLEAR	105-125VAC	1.5mA	25,000
WL-2150A3	AMBER	105-125VAC	1.5mA	25,000
WL-2150A4	WHITE	105-125VAC	1.5mA	25,000
WL-2152A5	GREEN	105-125VAC	1.5mA	25,000
WL-2152A6	BLUE	105-125VAC	1.5mA	25,000
NEON 230VAC SERIES				
WL-2151A1	RED	208-250VAC	1.5mA	25,000
WL-2151A2	CLEAR	208-250VAC	1.5mA	25,000
WL-2151A3	AMBER	208-250VAC	1.5mA	25,000
WL-2151A4	WHITE	208-250VAC	1.5mA	25,000
WL-2153A5	GREEN	208-250VAC	1.5mA	25,000
WL-2153A6	BLUE	208-250VAC	1.5mA	25,000
INCANDESCENT 12V SERIES				
WL-2194A1-12V	RED	12V-14V	80mA	25,000
WL-2194A3-12V	AMBER	12V-14V	80mA	25,000
WL-2194A4-12V	WHITE	12V-14V	80mA	25,000
WL-2194A5-12V	GREEN	12V-14V	80mA	25,000
INCANDESCENT 28V SERIES				
WL-2194A1-28V	RED	24V-28V	40mA	25,000
WL-2194A3-28V	AMBER	24V-28V	40mA	25,000
WL-2194A4-28V	WHITE	24V-28V	40mA	25,000
WL-2194A5-28V	GREEN	24V-28V	40mA	25,000

NOTES

1. Minimum panel thickness 0.030"
2. 6" leads with 1/2" strip are standard
3. Storage temperature
 T_{STG} : -25°C - +80°C
4. Ambient temperature
 T_A : -20°C - +60°C
5. Voltage tolerance
 V_{OP} : ±10%
6. AC operation only for neon type
7. AC/DC operation for incandescent type
8. Body material
Nylon, white
9. Lens material
Polycarbonate
10. Bezel finish
Chrome
11. Wire gauge
18 AWG
12. Wire strip
1/2"


CERTIFICATIONS

UL (E340667), RoHS



RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

