

T150LL9X2



Article Number: 111-15719

Heavy Duty Cable Tie, 36.4" Long, 175 lb Tensile Strength, PA66, Natural, 25/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	T150LL9X2
Type	T150LL
Color	Natural (NA)
Features and Benefits	• Heavy duty design to offer higher tensile strength. • Head design provides high tensile strength with very low insertion force.
Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Fixation Method (FF)	None
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Short Description	Heavy Duty Cable Tie, 36.4" Long, 175 lb Tensile Strength, PA66, Natural, 25/pkg

Product Dimensions

Minimum Tensile Strength (imperial)	175.0 lbs
Minimum Tensile Strength (N)	780.0 N
Length L (imperial)	36.4 "
Length L (metric)	925.0 mm
Width W (imperial)	0.35 "
Width W (metric)	8.8 mm
Bundle Diameter min (imperial)	0.32 "
Bundle Diameter min (metric)	8.0 mm
Bundle Diameter max (imperial)	10.8 "
Bundle Diameter max (metric)	275.0 mm
Thickness T (imperial)	0.079 "
Thickness T (Metric)	2 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	25
Carton Quantity	500
Weight (Metric)	18.4 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
CSA Certified	No
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Conformity	Yes
Certification/Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes