

LED Cool Light

240 Vac, 6W and 12W, UK Plug



- Equipped with a LED driver for directly connecting to AC power Voltage (100V~260V) (50Hz/60Hz)
- LED Driver can be externally mounted for increasing LED bulbs
- Reinforced Lense for high resistance
- Furnished with 1.8 meters cord with UK plug
- Long service life up to 40,000 hours
- Suitable for Semiconductors manufacturing equipment and clean room
- Temperature range -30°C to +60°C
- IP67 Rated

Built in Ballast Series

Stock No.	LED BULB QUANTITY	LIGHT OUTPUT	A	C	D	Ø
777-7996	1W x 6	780 lm	380mm	396mm	414mm	70mm
777-7990	1W x 12	1560 lm	658mm	674mm	692mm	70mm

