

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

RoHS

NOTES:

Insulator Material: PBT, UL

94V-0

Contact Plating: TiN, 80-100 μ "

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20M Ω Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000M Ω

Min.

Operating Temp.: -40°C~+105°C

NUMBER OF POSITIONS	DIMENSIONS	
	A	B
06	2.54	18.31
08	3.81	19.58
10	5.08	20.85
12	6.35	22.12
14	7.62	23.39
16	8.89	24.66
18	10.16	25.93
20	11.42	27.20
24	13.97	29.74
26	15.24	31.01
30	17.78	33.55
34	20.32	36.09
40	24.13	39.90
50	30.48	46.25
60	36.83	52.60
64	39.37	55.14

CnC Tech,LLC

3210-XX-003-11-99

SCALE SHEET UNIT





1:1

1/1

MM

DRW NO:

REV: A



P.C.B LAYOUT