




REV.	DATE	ECR NO.	DESCRIPTION
A	09/08/98	—	RE-DIMENSION DDRAWING, ADD CABLE STRIPPING DIMS.
B	07/23/99	—	UPDATE CABLE STRIPPING DIMENSIONS
C	06/02/08	100022	UPDATE DRAWING FORMAT



STEP-1

STRIP CABLE TO
RECOMMENDED DIMENSIONS



STEP-2

FOLD SHIELD BACK AS SHOWN.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	GRS	06/02/08							
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	CHECKED				PART DESCRIPTION F PLUG – 1 PIECE CRIMP – RG59/U					
6						ISSUED									
5					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	SHEET	1 OF 1			PART NO. 222117					
4															
3	SHELL	BRASS	NICKEL	1						DWG. NO. 222117.DWG					
2	HOUSING	BRASS	NICKEL	1											
1	BODY	BRASS	NICKEL	1						REV.	C	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING			C:/222/222117.DWG							