



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'F5PE10H-NM10'

Your search criteria matched only one product, shown below

F5PE10H-NM10



- Pass all TIA/EIA-568-B.3 performance requirements
 - Insertion loss per connection: 0.10dB typical; 0.30dB maximum
 - Include color-specific keys with positive and negative keying features to mechanically and visually distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
 - Part of a complete Keyed LC System that includes *Opti-Core*® Patch Cords and Pigtails, *OptiCam*® Pre-Polished Cam Connectors, *Opticom*® Fiber Adapter Panels (FAPs), and *Mini-Com*® Adapter Modules
 - Factory terminated and 100% tested for insertion loss
 - Insertion loss data recorded for every multimode patch cord
 - Lifetime traceability of test data to a Q.C. number on each patch cord
 - Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber
- Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact*

Customer Service for actual lead times.

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

• Part Number	F5PE10H-NM10
• RoHS Compliancy Status	RoHS directive is not applicable
• Note	Intended for use in fixed installations which are outside the scope of RoHS.
• Part Description	LC (keyed H - Aqua) to pigtail multimode duplex plenum pigtail, 1.6mm jacketed cable (one keyed LC connector on one end and open on the other end) – 50/125µm.
• Length (m)	10
• Fiber Compatibility	50/125µm
• Fiber Cable Size	1.6mm
• Fiber Cable Type	Jacketed
• Fiber Type	Multimode 50/125
• Cable Type	Duplex
• Connector 1 Type	LC Connector - Keyed H (Aqua)
• Connector 2 Type	Pigtail
• Fiber Count	2
• Flammability Rating	Plenum (OFNP)
• Key Type and Color	Keyed H Aqua
• No. of Fibers	2
• Pricing Description	LC (keyed H - Aqua) to pigtail 50µm OFNP dupl 1.6mm pigtail 10m
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.