


Technical drawing of a circular component, likely a valve or fitting, showing dimensions in inches and millimeters. The drawing includes a top view and a side view.

Top View Dimensions:

- Overall Diameter: 1.00 (25.4)
- Inner Diameter: .96 (24.4)
- Outer Diameter: .75 DIA. (19.1)

Side View Dimensions:

- Overall Height: .44 (11.2)



PANDUIT PART NUMBER	MAXIMUM CABLE DIAMETER	PANEL DIMENSIONS		WEIGHT
		THICKNESS	HOLE SIZE	LBS./100 PCS. (g)
SICH75	.75 (19.1)	.03/.10 (0.8/2.5)	.250 (6.4)	.24 (110)

① 1. SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE
AND PART COLOR.

CAD FILENAME/LAYERS

PANDUIT

SNAP-IN CLIP
SICH75

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	N/A	(.XXX) ±	.010 (.25)
(.XX) ±	.02 (.5)	ANGLES ±	N/A

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

	MAT'L:
--	--------

NYLON 6/6

DRAWING NO.

GB0239J0

DWG
A
SIZE

R	9/4/02	LGG		INITIAL RELEASE, REPLACED G-01546	GB0239JO	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	