


ASSY P/N	DESCRIPTION	ITEM A	ITEM A DESCRIPTION	CUT LENGTH (mm)	ITEM B	ITEM B DESCRIPTION
797580001	Micro-Fit Female (Sn) 20 AWG,UL1061,150MM	799442856	Wire 18AWG, UL1061	150 +/- 5	39000038	Mini-Fit Female (Sn)
797580002	Mini-Fit Female (Sn) 18 AWG,UL1061,150MM	799442113	Wire 20AWG, UL1061	150 +/- 5	430300001	Micro-Fit Female (Sn)
797580003	SL Female (Sn) 22 AWG,UL1061,150MM	799442856	Wire 22AWG, UL1061	150 +/- 5	16020086	SL Female (Sn)
797580004	Micro-Fit Female (Au) 20 AWG,UL1061,150MM	799442113	Wire 20AWG, UL1061	150 +/- 5	430300003	Micro-Fit Female (Au)
797580005	Mini-Fit Male Tin (Sn) 18 AWG,UL1061,150MM	799442625	Wire 18AWG, UL1061	150 +/- 5	39000040	Mini-Fit Male Tin (Sn)
797580006	PicoBlade 26 AWG,UL1061,150MM	799442625	Wire 26AWG, UL1061	150 +/- 5	500798000	PicoBlade
797580007	KK Hot Tin (Sn) 22 AWG,UL1061,150MM	799442332	Wire 22AWG, UL1061	150 +/- 5	08500113	KK Hot Tin (Sn)
797580008	Pico-SPOXFemale (Sn)24 AWG,UL1061,150MM	799443305	Wire 24AWG, UL1061	150 +/- 5	874210000	Pico-SPOX Female (Sn)
797580009	Mini-Fit Female (Sn) 18 AWG,UL1061,300MM	799442856	Wire 18AWG, UL1061	300 +/- 5	39000038	Mini-Fit Female (Sn)
797580010	Micro-Fit Female (Sn) 20 AWG,UL1061,300MM	799442113	Wire 20AWG, UL1061	300 +/- 5	430300001	Micro-Fit Female (Sn)
797580011	SL Female (Sn) 22 AWG,UL1061,300MM	799442332	Wire 22AWG, UL1061	300 +/- 5	16020086	SL Female (Sn)
797580012	Micro-Fit Female (Au) 20 AWG,UL1061,300MM	799442113	Wire 20AWG, UL1061	300 +/- 5	430300003	Micro-Fit Female (Au)
797580013	Mini-Fit Male Tin (Sn) 18 AWG,UL1061,300MM	799442856	Wire 18AWG, UL1061	300 +/- 5	39000040	Mini-Fit Male Tin (Sn)
797580014	PicoBlade 26 AWG,UL1061,300MM	799442625	Wire 26AWG, UL1061	300 +/- 5	500798000	PicoBlade
797580015	KK Hot Tin (Sn) 22 AWG,UL1061,300MM	799442332	Wire 22AWG, UL1061	300 +/- 5	08500113	KK Hot Tin (Sn)
797580016	Pico-SPOX Female (Sn)24 AWG,UL1061,300MM	799443305	Wire 24AWG, UL1061	300 +/- 5	874210000	Pico-SPOX Female (Sn)



NOTES :

- 1 THE PRODUCT SPECIFICATION OF HARNESS RELIES ON THE CONNECTOR, TERMINALS AND WIRE SPEC.
2 ROHS AND LEAD FREE COMPLIANT
3 SPECIAL REQUIEREMENT: N/A

ROHS COMPLIANT

ENTER DESCRIPTION EC NO: MEX2010-0030 DRWN:SMARTINEZ 2010/01/12 CHKD:ACUEVAS 2010/01/12 APPR:ACUEVAS 2010/01/13 REV A	QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY SMARTINEZ	DATE 2010/01/12	TITLE PRE-CRIMPED LEADS AMERICAS DISTRIBUTION CHANNEL REV : A			
		4 PLACES	± ---	± ---	CHECKED BY ACUEVAS	DATE 2010/01/12				
		3 PLACES	± ---	± ---	APPROVED BY ACUEVAS	DATE 2010/01/12	MOLEX INCORPORATED			
		2 PLACES	± ---	± ---	MATERIAL NO. 79758XXXX					
1 PLACE		± ---	± ---	SIZE A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								