

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200980207](#)
Status: **Active**
Overview: [PROFIBUS Solutions](#)
Description: PROFIBUS Straight Male D-Sub to Dual 90° Male D-Sub, 22 AWG, PUR Cable, 1.0m (3.28') Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Cordsets
Series	120098
Connector End A	D-Sub (9-pin)
Connector End B	Dual D-Sub (9-pin)
IP Rating	IP40
Material - Contact	N/A
Overview	PROFIBUS Solutions
Product Name	PROFIBUS
Protocol	N/A
Region	America, Asia, Europe
Type	Double Ended
UPC	78172504523
Physical	
Cable Diameter	8.00mm (.315")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Purple
Coupling Style	Threaded
Gender	Male-Male/Male
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	N/A
Material - Coupling Nut	Gray Anodized Aluminum
Material - Plating Mating	N/A
Orientation	90°/90° to Straight
Poles	9
Temperature Range - Operating	0°C to +60°C
Wire Size AWG	22
Wire/Cable Type	Shielded-Twisted Pair
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	MM3G61PP4M010
Reference - Drawing Numbers	
Sales Drawing	SD-120098-021



Series image - Reference only

<u>EU ELV</u> Not Reviewed	
<u>EU RoHS</u> Not Reviewed	<u>China RoHS</u>
<u>REACH SVHC</u> Not Reviewed	
<u>Halogen-Free</u> <u>Status</u> Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120098](#) Series