




	Cable Type	Diameter A	Diameter B	For Cable Diameter
5155 Series	RG 58, 141	.23 (5,84) x .51 (12,95) Deep	.21 (5,33)	.185" - .200"
5156 Series	RG 59, 62, 210	.28 (7,11) x .26 (6,60) Deep	.26 (6,60)	.237" - .247"
5157 Series	RG 174, 187, 188	.160 (4,06) x .51 (12,95) Deep	.12 (3,05)	.090" - .110"

MATERIALS:

PVC

Marking: "POMONA ELECTRONICS"

RATINGS:

Operating Temperature: +50C°. (+122°F.) Max.

ORDERING INFORMATION: Model 5155-*, 5156-*, 5157-*

*=Color Code, -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, --7 Violet, -8 Gray, -9 White

Sold in packages of 10

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA