


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	B HEIGHT	IMPRINT AREA C	VERTICAL REPEAT D	LABELS PER ROW	STANDARD PKG. QTY.
S200X400TAT	GMT1	4.000 [101.6]	1.00 +/- .031 [25.4]	4.250 [108.0]	2	500



- NOTES:
 1. SEE MFG. DRAWING NO. A61297.
 2. MILLIMETERS ARE IN [].



UNWIND
DIRECTION

CAG FILENAME/LAYERS I00472KX_C10325_S200X400TAT_00.PRT									
PANDUIT CORP TINLEY PARK, ILLINOIS									
OPTIMUM SELF-LAM. S200X400TAT THERMAL TRANSFER PRINTABLE LABELS									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .005 (.XX) ± .015 ANGLES ±					UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION				
DRAWN BY RVU		MAT'L:		SCALE NTS		DRAWING NO. C10325		DWG SIZE B	
DATE 10-12-04		SEE TABLE							
CHK'D									

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	10-12-04	RVU		DRAWING RELEASED.	0000	R		