

Pre-Assembled C2 Cabinet *C2RR Series*



Features

- Constructed in:
 - 14-gauge steel (body)
 - 16-gauge steel (doors and side panels)
 - 10-gauge steel (tapped mounting rails)
 - 12-gauge steel (square hole mounting rails)
- Finished in a rugged, textured powder paint finish.
- Tested to nearly double the suggested load rating of 1,500 lbs (680 kg).
- RoHS Compliant.
- Manufactured in North America.
- **All configurations include:**
 - One (1) Welded C2 Cabinet Frame
 - Two (2) Removable Side Panels (with 1/4 turn latches)
 - Four (4) Leveling Feet
 - Eight (8) Keys
 - Starter pack of 10-32 Screws (and cage nuts when applicable).
- **C2RR Series Specific Components Include:**
 - Four (4) Infinitely Adjustable - Tapped 10-32 Combination Mounting Rails
 - One (1) Solid Locking Door
 - One (1) Solid Top Panel
- **C2RR "D" Series Specific Components include:**
 - Four (4) Infinitely Adjustable - Tapped 10-32 Combination Mounting Rails
 - One (1) Window Front Locking Door
 - One (1) Louvered Rear Locking Door
 - One (1) Vented Top Panel with Four (4) 3.5" (89 mm) diameter cable access holes with covers

Gallery



Accessories

- C2 Doors
- Door Adapter Cable Entry Kit
- Side Panel Locking Kit
- Cabinet Baying/Ganging/Joining Kit
- Shelves
- Door Adapter Rack Mount Kit
- Cabinet Fan Tops
- Cabinet Door Replacement Lock
- C2/C3 Bolt Down Kit
- Rack Mount Locking Storage Drawer

- Vertical Cabinet Cable Manager with Door
- Cable Lacing Bar
- Horizontal Hinged Cable Manager
- Cable Management Arm
- Mounting Hardware
- Rack Panels
- Medium Caster Set
- Vertical Cable Tray
- Horizontal Lacing Strip
- Horizontal Ring Cable Manager
- Outlet Strips
- Grounding
- Caster Set

C2RR Rapid Rack

Part No. Black	Part No. Light Gray	Overall Dimensions			Usable Mounting Dimensions			Rack Units	Shipping Weight (lbs)
		Height	Width	Depth	Height	Width	Depth		
C2RR194223BK1	C2RR194223LG1	50.16	23.00	23.62	42.06	19.00	21.63	24U	170
C2RR194231BK1	C2RR194231LG1	50.16	23.00	31.50	42.06	19.00	29.50	24U	194
C2RR196323BK1	C2RR196323LG1	71.16	23.00	23.63	63.06	19.00	21.63	36U	218
C2RR196331BK1	C2RR196331LG1	71.16	23.00	31.50	63.06	19.00	29.50	36U	250
C2RR197023BK1	C2RR197023LG1	78.16	23.00	23.62	70.06	19.00	21.63	40U	230
C2RR197031BK1	C2RR197031LG1	78.16	23.00	31.50	70.06	19.00	29.50	40U	268
C2RR197823BK1	C2RR197823LG1	86.91	23.00	23.62	78.81	19.00	21.63	45U	254
C2RR197831BK1	C2RR197831LG1	86.91	23.00	31.50	78.81	19.00	29.50	45U	290

Overall height includes leveling feet.

C2RR "D" Series LAN/Data Rapid Rack

Part No. Black	Part No. Light Gray	Overall Dimensions			Usable Mounting Dimensions			Rack Units	Shipping Weight (lbs)
		Height	Width	Depth	Height	Width	Depth		
C2RR197023DBK1	C2RR197023DLG1	77.31	23.00	23.63	70.06	19.00	21.63	40U	295
C2RR197031DBK1	C2RR197031DLG1	77.31	23.00	31.50	70.06	19.00	29.50	40U	315
C2RR247023DBK1	-	77.31	28.00	23.63	70.06	24.00	21.63	40U	325
C2RR247031DBK1	-	77.31	28.00	31.50	70.06	24.00	29.50	40U	346
C2RR197823DBK1	C2RR197823DLG1	86.06	23.00	23.63	78.81	19.00	21.63	45U	330
C2RR197831DBK1	C2RR197831DLG1	86.06	23.00	31.50	78.81	19.00	29.50	45U	355
C2RR247823DBK1	-	86.06	28.00	23.63	78.81	24.00	21.63	45U	342
C2RR247831DBK1	-	86.06	28.00	31.50	78.81	24.00	29.50	45U	363

Overall height includes leveling feet.

Data subject to change without notice