



Stainless Steel 2-Piece Ball Valve with Pneumatic Actuator – Double Acting


1,000 PSI Rated




Materials

Body	=	CF8M - 316 S/S
Ball	=	316 S/S
Stem Seal	=	PTFE
Ball Seal	=	PTFE


Pressure - Temperature Diagram



"NAMUR" connection for solenoid valve.



Holes according ISO 5211.



Overall Dimensions - Double Acting

RS Part No.	Dia mm	Size ins.	Model	A	B	D	ØE	F	L	ØM
	8	1/4"	AP0 - DA	65	122.5	36	32.4	9.6	110	11
	10	3/8"	AP0 - DA	65	122.5	36	32.4	9.6	110	12.7
	15	1/2"	AP0 - DA	65	122.5	38	34.6	12	110	15
	20	3/4"	AP0 - DA	74.5	135.7	41.7	43.9	19	110	20
	25	1"	AP1 - DA	88.5	161.6	44.4	50.3	19.5	137	25
	32	1 1/4"	AP2 - DA	102	193.3	54	62.6	20.3	150	32
	40	1 1/2"	AP2 - DA	110	204.6	59.5	74.1	24.5	150	40
	50	2"	AP3 - DA	125	236.6	67	89.1	29	204	50