



										1
LOC	DIST	P	F	REVISIONS						
G	14			ZONE	LTR	DESCRIPTION			DATE	APPD
					F	REV & REDRAWN PER 0720-0040-93			3-24-93	1AP DAP



METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL Listed
6HD AWG SOLID OR STRANDED	6HD AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
6HD AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 6HDW* APPROX AS SHOWN

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
10.5-16.8MM² [20,800-33,100] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -

MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH
TIN PLATE
0.00254[.000100] MIN
THK PER MIL-T-10727

DR 3-24-93
TA BRINKMAN
CHK 3-24-93
DA PATTERSON

APPD 3-24-93
DE MILLER
APPD 3-24-93
JL MECKLEY

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT -

#10	5.00±0.08 DIA [.197±.003]	2-330969-1
1/4	6.73±0.13 DIA [.265±.005]	330969
STUD SIZE	"H"	PART NO
AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME TERMINAL, RING TONGUE, HEAVY DUTY, SOLISTRAND™		
SIZE ©	CAGE CODE 00779	DRAWING NO ©=330969
SCALE 4:1	SHEET 1 OF 1	