



Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFFiber Optic ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'F5LZ6P-12M5'

Your search criteria matched only one product, shown below

F5LZ6P-12M5



- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F5LZ6P-12M5
RoHS Compliancy Status	Compliant
Part Description	FJ® Plug to female MTRJ multimode duplex LSZH patch cord, 1.8mm jacketed cable (one FJ® Plug on one end and one female MTRJ connector on the other end)— 50/125μ m.
Product Type	Hybrid Patch Cords
Length (m)	5
Fiber Compatibility	50/125μm
Fiber Cable Size	1.8mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode
Connector 1 Type	FJ® Plug
Connector 2 Type	MT-RJ Connector
End Configurations	FJ® Plug to MTRJ
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.