




AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
170° C MAX

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

VOLTAGE RATING:

NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64²mm[5,180-13,100] CIR MILS
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	DK SCHRUM	05JUL94
CHK	DA PATTERSON	08AUG94
APVD	CH KULYNYCH	08AUG94

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES ± -	

MATERIAL	FINISH
COPPER PER ASTM B-152 ANNEALED	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727

WEIGHT	-
CUSTOMER DRAWING	

NAME	TE Connectivity		
TERMINAL, KNIFE DISCONNECT, BUDGET			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-31939	-

SCALE	10:1	SHEET	1 OF 1	REV	B1
-------	------	-------	--------	-----	----