


LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	PART NUMBERS CHANGED TO TYCO	24MAR2003	ACK	G.F.



HIGH FLEXIBILITY FLAT CABLE

WIRE SIZE	32 AWG FLAT CONDUCTOR (0.65mm x 0.05mm)
CONDUCTOR GRID	1.27mm
INSULATION	POLYESTER, PINK
TEMPERATURE RATING	-40° TO +80° C
VOLTAGE RATING	90 V rms

REEL LENGTH 30.5m				
TYCO - PN	OLD PN		DIM. A	DIM. B
0-1437380-1	175-06G		7.6	6.35 ±0.18
0-1437380-2	175-10G		12.7	11.43 ±0.18
0-1437380-3	175-14G		17.8	16.51 ±0.18
0-1437380-4	175-16G		20.3	19.05 ±0.25
0-1437380-5	175-20G		25.4	24.13 ±0.25
0-1437380-6	175-26G		33.0	31.75 ±0.25
0-1437380-7	175-34G		43.2	41.91 ±0.25
0-1437380-8	175-36G		45.7	44.45 ±0.25
0-1437380-9	175-37G		47.0	45.73 ±0.25
1-1437380-0	175-40G		50.8	49.53 ±0.38
1-1437380-2	175-50G		63.5	62.23 ±0.38
1-1437380-4	175-60G		76.2	74.93 ±0.38
1-1437380-5	175-64G		81.3	80.01 ±0.38

FLAT CABLE FOR USE WITH ANSLEY 609 SERIES CONTACTS ONLY.
REQUIRES CABLE GUIDE ADAPTER FOR CORRECT TERMINATION.
609-WXX4 FOR SOCKET CONNECTORS (609-XX00M)
AND 609-WXX3 FOR PCB TRANSITION CONNECTORS (609-XXX3).
FOR ADAPTER SEE DRAWING 3-1437758-7

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	24MAR2003	tyco tyco Electronics AMP GmbH Electronics D - 67346 Speyer	
		CHK	26MAR2003		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.1	APVD	28MAR2003	NAME HIGH FLEXIBILITY FLAT CABLE ANSLEY 175 SERIES 32 AWG	
		PRODUCT SPEC			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APPLICATION SPEC		SIZE A3	
		WEIGHT			
MATERIAL	FINISH	CUSTOMER DRAWING		SCALE	20:1
-	-			SHEET	1 OF 1
				REV	A1