




MATERIAL:
BODY & COVER - 16 GA. [1.5mm] C.R.S.
INTERNAL PANEL - 14 GA. [2.0mm] C.R.S.
WALL MOUNTING BRACKETS - 14 GA. [2.0mm] TYPE 304 STAINLESS STEEL
STRIKERS - C.R.S.
HINGE PINS & WALL MOUNTING HARDWARE - STAINLESS STEEL
LATCHES - ZINC DIE CAST
GASKET - 0.25 [6.3] THK. NEOPRENE
SEALING WASHERS - BLACK NEOPRENE OR EQUIVALENT

FINISH:
BODY & COVER - LIGHT GRAY SMOOTH POWDER COAT
INTERNAL PANEL - ZINC PLATED
WALL MOUNTING BRACKETS & HINGE PINS - NATURAL
STRIKERS - ZINC PLATED
LATCHES - CHROME PLATED

PART NO.	"A"	"B"	"C"	"D"	"E"	"F"	"G"	"H"	"J"	"K"	"L"	"M"	"N"
SNB-3737	15.75 [400]	15.75 [400]	7.87 [200]	7.29 [185.1]	17.02 [432.3]	14.29 [363]	14.16 [359.5]	14.16 [359.5]	12.80 [325]	12.80 [325]	14.37 [365]	13.78 [350]	11.62 [295]
SNB-3743	15.75 [400]	13.98 [355]	7.87 [200]	7.29 [185.1]	17.02 [432.3]	12.52 [318]	14.16 [359.5]	12.38 [314.5]	12.80 [325]	11.03 [280]	14.37 [365]	12.00 [305]	11.62 [295]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[SNB-3737-SS](#)