



712 Combustion Analyzer

Features

QUICK AND SIMPLE SET UP All TPI analyzers feature quick and simple set up. Fast purge and the ability to perform fuel selection during start up enable tests to be performed quickly without requiring extra set-up time after initial start-up. TPI analyzers also use the last selected fuel as the default setting. This feature prevents the need to perform fuel selection every time the analyzer is turned on.

- Built-in differential manometer with 0.001" H₂O resolution
- Calculates combustion efficiency
- Data Logging with time and date stamp
- Will not shut off if 15 ppm CO is present for increased safety
- Communicate to a PC via the optional A767 IR interface
- Optional A740 IR printer available for hard copies of test results
- Built-in differential thermometer
- Store function to save up to 50 readings
- Pump driven for fast response
- Push on fittings for fast and easy use
- Large easy to read backlit display
- Ten selectable fuels

Specifications

Instrument

Operating Temperature Range	14°F to +122°F (-10°C to +50°C)
Battery / Battery Life	Rechargeable Ni-MH / > 6 Hours
Charger Input Voltage	115V or 230V : 50/60 Hz AC
Fuels	Natural Gas, LPG, Light Oil, Heavy Oil, Bituminous Coal, Anthracite Coal, Coke, Butane, Wood, Bagasse
Units of Pressure	mbar, kPa & inH ₂ O
Display	3 Line Backlit LCD w/ annunciators
Data Storage	10 sets of readings
Data Logging	400 sets of readings
Single Logging	150 sets of readings
Time & Date	24 Hour Real Time Clock
Dimensions	7.8" x 3.5" x 2.4"
Weight	1.1lbs

Gases

	Range	Resolution	Accuracy
Oxygen	0-25%	0.1%	+/- 0.3%
Carbon Monoxide	0-10,000 ppm	1 ppm	+/- 5 ppm or 5%
Carbon Dioxide	0-25%	0.1%	Calculated
CO/CO ₂ Ratio	0-0.999	0.001	Calculated
Combustion Eff.	0-100%	0.1%	Calculated
Gas Leak Sensor	100-10,000 ppm		

Pressure Measurement

Selectable Ranges	mbar, kPa and inH ₂ O
Range	-120 inH ₂ O to 120 inH ₂ O
Resolution	0.001 inH ₂ O
Accuracy	+/- 0.5% fsd

Temperature Measurement

Input Type	K-Type thermocouple
Range	-58°F to 1832°F (-50°C to 1000°C)*
Resolution	1°F (1°C)
Accuracy	+/- (0.3% of rdg + 2°F) or +/- (0.3% of rdg + 1°C)

712 Contents

712 Combustion Analyzer



A787 Soft Carrying Case



A776 Static Tip (2)



A774 Silicone Tubing



A791 Adapter tubing



A603 Brass Hose Barb Fitting (2)



A611 Gas Valve Pressure Adapter



GK11M K-type thermocouple



A770 Flue Probe



A763 Mini pump protection filter

