


MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

SWITCH - TOGGLE


CATALOG LISTING
12TS95127 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH



CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN		
	KEYWAY SIDE (1-2,4-5)	CENTER (1-2,4-5)	OPPOSITE KEYWAY (2-3,5-6)
12TS95127-1	ON	OFF	ON
12TS95127-2	OFF	NONE	ON
12TS95127-3	ON	NONE	ON
12TS95127-21	NONE	OFF	ON
12TS95127-31	NONE	ON	ON
12TS95127-4	MOM OFF	NONE	ON
12TS95127-5	MOM ON	OFF	ON
12TS95127-6	MOM ON	NONE	OFF
12TS95127-7	MOM ON	OFF	MOM ON
12TS95127-8	MOM ON	NONE	ON
12TS95127-51	NONE	ON	MOM ON
12TS95127-61	MOM ON	OFF	NONE

ELECTRICAL DATA	
L312	
10A 277 VAC, 20A 125 VAC	
1.5 HP 125, 250 VAC	
10A-125, 250, 277 VAC	
1/4HP-125VAC; 1/2HP-250, 277 VAC	
3A-125VAC "L" CODE L192	



- NOTES
- △ FURNISHED UNASSEMBLED
 - 2 - CIRCUIT DESIGNATION AND MICRO SWITCH CAT. LISTING MARKED ON SIDE OF SWITCH
 - 3 - SWITCH TERMINALS MAY BE USED WITH AMP RECEPTACLE NO. 41194 (OR EQUIVALENT)
 - 4 - NUMBER 5 TERMINAL ROTATED 180° (BLADE OF TERMINAL FACING CENTER OF SWITCH)

THIRD ANGLE PROJECTION	
SCALE	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.01) ±.030
TWO PLACE	(.00) ±.015
THREE PLACE	(.000) ±.005
ANGLES	±
WEIGHT	.10 LB MAX