


REV.	ECN.	NO.	APPD.
X1	TBD	02/10'11	



WIRE TABLE

J1	CONNECTION	J2	REMARK
1	RED	1	VBUS
2	WHITE	2	D-
3	GREEN	3	D+
4	BLACK	4	GND
5	BLUE	5	STP1-
6	YELLOW	6	STP1+
7	DRAIN	7	GND
8	PURPLE	8	STP2-
9	ORANGE	9	STP2+
SHELL	BRAID	SHELL	

RAW CABLE SPEC.

RAW CABLE P/N	SDPAWG	UTPAWG	PowerAWG	OD mm	Color
791-1002-035	28	28	24	5.4	BLACK

NOTES:

- ANY OPEN,MISSWIRING&SHORTARE NOT PERMITTED, PRODUCT 100% TEST.
- INSULATION RESISTANCE: 100M OHM(MIN)/300VDC, CONTACT RESISTANCE: 2.0 OHMS(MAX)
- HARMFUL MATERIAL CONTROL PLEASE FOLLOW Doc.No."EPI12".

FOXCONN CONFIDENTIAL

9	USB 3.0 B PLUG CONN.	1	UC2090C-K05-4F	HOUSING: PBT, COLOR BLUE.
8	USB 3.0 B PLUG FRONT SHELL	1	024-0001-1096	100u" Min. Ni OVER THE SURFACE
7	USB 3.0 B PLUG REAR SHELL	1	024-0001-1095	NI AND SN PLATING
6	USB 3.0 B PLUG OVER MOLD	A/R	901-3208-024	UL 94V-0, PVC BLACK
5	RAW CABLE	A/R	791-1002-035	SHOW AS RAW CABLE SPEC.
4	USB 3.0 A PLUG OVER MOLD	A/R	901-3208-024	UL 94V-0, PVC BLACK
3	USB 3.0 A PLUG CONN.	1	075-0001-238	CONTACT: Au 30".
2	USB 3.0 A PLUG REAR SHELL	1	024-0001-8881	SPCC T=0.3MM
1	USB 3.0 A PLUG FRONT SHELL	1	024-0001-8880	SPCC T=0.3MM
NO	DESCRIPTION	Q'TY	P/N	REMARK
X.±	X°.±	UNITS	mm	NAME<INTENDED USE>
.X± 0.2	.X°.±	MAT'L		CUSTOMER DRAWING
.XX±	.XX°.±			PART NO.<INTENDED USE>
.XXX±	.XXX°.±	FINISH		CUED005F-K25-0F
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON HAI PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON HAI PRECISION IND. CO., LTD.				APPD:
				CHKD:
				DR: Xianhui Lei 02/10 '11
				605-*
				SCALE SHEET REV.
				NONE 1/1 X1

