



+ CONNECTORS

CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
.64MM,32P UNSEALED PLUG ASSY,B
TH/.025 Connector System

1326018-2
TE Internal Number: 1326018-2

EU RoHS Compliant
EU ELV Compliant

Connector System Wire-to-Wire
Connector Style Housing for female terminals
Mating Tab Width .64 mm [.025 in]
Sealable No
Centerline (Pitch) (in) .1

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings
PLUG ASSEMBLY, 32 POSITION, UNSEALED, 0.64mm CONNECTOR
PDF
English

CAD Files
3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English
Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Instruction Sheets

Instruction Sheet (U.S.)

0.64 Mm Automotive 32-Position Plug Connector Assembly

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Connector System** Wire-to-Wire
- Connector Style** Housing for female terminals
- Sealable** No
- Hybrid Connector** No
- Primary Locking Feature** Integrated in Housing
- Strain Relief** No
- Row-to-Row Spacing** 5.9 mm [.232 in]

Configuration Features

- Number of Rows** 4

Body Features

- Color** Yellow
- Cable Exit Angle** 180°
- Body Material** PA GF

Contact Features

- Mating Tab Width** .64 mm [.025 in]

Mechanical Attachment

- Mounting Feature** No
- Terminal Position Assurance** Yes
- Polarized** No

Housing Features

- Centerline (Pitch) (in)** .1
- Pitch (mm)** 2.54

Dimensions

Width 42 mm [1.6535 in]
Height 34 mm [1.34 in]
Length 42 mm [1.6535 in]

Usage Conditions

Operating Temperature (Max) (°C) 70, 75, 80, 85, 90, 100, 105
Operating Temperature (Max) (°F) 158, 167, 176, 185, 194, 212, 221
Operating Temperature Range (°F) -40 – 221

Operation/Application

Circuit Application Signal

Industry Standards

Degree of Protection Other
UL Flammability Rating UL 94-HB
Agency/Standard SAE/USCAR-2

Packaging Features

Packaging Method Package
Packaging Quantity 80

Other

Connector Position Assurance Capable Yes
Serviceable No

Statement of Compliance

Statement of Compliance
PDF