

SCALE: 1" = 1.5"

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN MM
TOLERANCES:
.XX-- ± 1
.XXX-- ± .5
ANGLE-- ± 3°

1).Contact Rating:
NO: 30 A, 277 V AC, Resistive
16 FLA, 277 V AC
1 HP, 120 VAC
2 HP, 277 VAC

2).Coil Rated Voltage:
24VDC

Pick-Up: During 75%~110% coil rated voltage should pick up reliably
Drop-Out: During 10%~70% coil rated voltage should drop out reliably


3).Coil Resistance:
310 Ω ± 10%

4).Insulation class:
Class F Insulation

5).Service Life:
Mechanical Life 1,000,000 Operations
Electrical Life 100,000 Operations

6).Mark Approved :
UL : E251539

Contact Configuration



REV	Description	By	ECO #	Date

Goodspec		HongLi		
			Electric	
DRAWN BY: Zhao Ping	DATE: 04/20/2009	TITLE: RELAY, DPST, 24VDC	DRAWING NO: HLR-72ACTAA	SHEET REV.