

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS

RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.


REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓			O	RLSD PER DFTG REQUEST 84-6	6-12-84	TB/
✓			A	REV PER ECN CM. 54	7-20-85	RS/RS
✓			B	OBSOLETE -24-3 CM-473	6-14-86	Kw / RS
✓			C	OBSOLETE -4 PER CM-862	9-3-87	PKS /

△ NICKEL PLATED ON ENTIRE TERMINAL,
.000030 GOLD OVER INSIDE OF MATING AREA
AND WIRE BARREL.

2. WIRE RANGE: 18-24 AWG.

3. INSULATION RANGE: .100 MAX.



GOLD	△	.010 BRASS	61473 - 5
PRE-TIN		.010 BRASS	61473 - 1
FINISH		MATERIAL	PART NO.

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS ± .005
ANGLES ± .005

CONTRACT NO

OR *T Beck* 6/12/84CHK *M. Jones* 6/12/84APPD *R. L. Jones* 6/13/84

APPD

DSGN APPD

OTHER APPD

MATERIAL

SEE TABLE

FINISH

SEE TABLE

AMP

AMP INCORPORATED
Harrisburg, Pa.

NAME

SOCKET, COMMERCIAL MATE-
N-LOK, LOOSE PIECE

SIZE

B

FSCM NO

00779

DRAWING NO

61473

SCALE 5:1

SHEET

CUSTOMER DRAWING