

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300100519

Status:


Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 16 AWG, PVC Cable, 0.91m (3.0') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR6837
UL		E152210
General		
Product Family		Industrial Cordsets
Series		130010
Connector End A		Mini-Change
Connector End B		Mini-Change
IP Rating		IP67
Material - Contact		Brass
Overview		Brad Mini-Change Connectors
Product Name		Mini-Change
Protocol		DeviceNet
Region		America
Type		Double Ended
UPC		78678832606
Physical		
Cable Diameter		10.41mm (.410")
Cable Length		0.91m (3.0')
Color - Cable Jacket		Yellow
Coupling Style		Threaded
Gender		Female-Male
Keyway		Single
LED Indicator		No
Material - Cable Jacket		PVC
Material - Connector Body		PVC
Material - Coupling Nut		Black Epoxy Coated Zinc
Material - Plating Mating		Gold
Net Weight		125.000/g
Orientation		Straight to Straight
Poles		4
Temperature Range - Operating		-20°C to +105°C
Wire Size AWG		16
Wire/Cable Type		STOOW
Electrical		
Current - Maximum per Contact		10.0A
Voltage - Maximum		600V
Material Info		
Engineering Number		114020A01F030
Reference - Drawing Numbers		
Sales Drawing		SD-130010-005

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

130010 Series

This document was generated on 01/20/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION