

Type Designation	4903
Designation IEC	LR03
System	Zn-MnO ₂ (Alkaline)
Shelf Life (Coding)*	5 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	1240 (discharge with high-resistance)
Permissible Temperature Range	-10 °C ... 50 °C
Weight, approx. [g]	11
Volume [ccm]	3.8

Dimensions [mm]


min: max:

Ø	9.5	10.5
A	-	44.5
B	43.3	-
C	4.3	-
E	-	0.5
F	-	3.8
G	0.8	-

Discharge Type:

4 M/H, 8 H/D, 7 D/W
Portable Lightning


Load: 5,1 Ohm



Discharge Type:

15 S/M, 8 H/D, 7 D/W
Remote Control

Load: 24 Ohm



Discharge Type:

4 H/D, 7 D/W
Radio

Load: 75 Ohm

