




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		U	REV PER ECO-15-016062	09NOV15	KG	CD



- THIS PLUG IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 - MAX WIRE INSUL. TO BE USED WITH THIS PLUG IS .054 DIA.
 - METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
 - PACKAGE MARKED M 24308/4-329F
 - THIS PLUG WILL ACCEPT SIZE 22 PIN CONTACT M 24308/13 OR AMP # 204370
- AMP PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- UL/CSA DESIGNATION MARKED IN THIS AREA.

SUPERSEDED BY 204525-1	PHENOLIC, COLOR: BLACK	204525-2
	POLYPHENYLENE SULFIDE (PPS) CST-40F PER MIL-M-24519 OR GLASS FILLED POLYESTER TPES013G30 PER ASTM D5927 COLOR, BLACK	204525-1
	INSERT MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12-3-87 C.C.THOMAS	TE TE Connectivity			
DIMENSIONS: INCHES		CHK 1-25-88 F.BALLEW III				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME			
		PRODUCT SPEC -	AMPLITE PLUG FOR PIN CONTACTS HI-DENSITY D CONN, SIZE 1, SERIES 90, WITH FLOAT BUSHINGS			
		APPLICATION SPEC -	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT -	A2 00779	C=204525	-	-
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV U		