




DUAL-IN-LINE SOCKETS

SERIES 115...001 • VERY LOW PROFILE • OPEN FRAME



- Low profile DIP socket, sits only .122" above the PCB
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 115 uses MM #0501 pins. See page 162 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION																	
	A	B	C																			
10	0.5	0.2	0.3	41	115-XX-210-41-001000																	
4	0.2	0.3	0.4	102	115-XX-304-41-001000																	
6	0.3	0.3	0.4	67	115-XX-306-41-001000																	
8	0.4	0.3	0.4	50	115-XX-308-41-001000																	
10	0.5	0.3	0.4	40	115-XX-310-41-001000																	
14	0.7	0.3	0.4	28	115-XX-314-41-001000																	
16	0.8	0.3	0.4	25	115-XX-316-41-001000																	
18	0.9	0.3	0.4	22	115-XX-318-41-001000																	
20	1.0	0.3	0.4	20	115-XX-320-41-001000																	
22	1.1	0.3	0.4	18	115-XX-322-41-001000																	
24	1.2	0.3	0.4	16	115-XX-324-41-001000																	
28	1.4	0.3	0.4	14	115-XX-328-41-001000																	
20	1.0	0.4	0.5	20	115-XX-420-41-001000																	
22	1.1	0.4	0.5	18	115-XX-422-41-001000																	
24	1.2	0.4	0.5	16	115-XX-424-41-001000																	
28	1.4	0.4	0.5	14	115-XX-428-41-001000																	
32	1.6	0.4	0.5	12	115-XX-432-41-001000																	
24	1.2	0.6	0.7	16	115-XX-624-41-001000																	
28	1.4	0.6	0.7	14	115-XX-628-41-001000																	
32	1.6	0.6	0.7	12	115-XX-632-41-001000																	
36	1.8	0.6	0.7	11	115-XX-636-41-001000																	
40	2.0	0.6	0.7	10	115-XX-640-41-001000																	
42	2.1	0.6	0.7	9	115-XX-642-41-001000																	
48	2.4	0.6	0.7	8	115-XX-648-41-001000																	
50	2.5	0.6	0.7	8	115-XX-650-41-001000																	
52	2.6	0.6	0.7	7	115-XX-652-41-001000																	
50	2.5	0.9	1.0	8	XX=Plating Code See Below								RoHS-2 2011/65/EU									
52	2.6	0.9	1.0	7											115-XX-950-41-001000							
64	3.2	0.9	1.0	6											115-XX-952-41-001000							
SPECIFY PLATING CODE XX =						91	93			41 ◆	43 ◆											
Sleeve (Pin) 						200 μ" Sn/Pb	200 μ" Sn/Pb			200 μ" Sn	200 μ" Sn											
Contact (Clip) 						10 μ" Au	30 μ" Au			10 μ" Au	30 μ" Au											

XX=Plating Code
See Below

RoHS-2
2011/65/EU



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[115-43-964-41-001000](#) [115-43-952-41-001000](#) [115-43-950-41-001000](#) [115-43-652-41-001000](#) [115-43-650-41-001000](#) [115-43-648-41-001000](#) [115-43-642-41-001000](#) [115-43-636-41-001000](#) [115-43-432-41-001000](#) [115-43-428-41-001000](#) [115-43-424-41-001000](#) [115-43-422-41-001000](#) [115-43-420-41-001000](#) [115-43-322-41-001000](#) [115-43-310-41-001000](#) [115-43-306-41-001000](#) [115-43-304-41-001000](#) [115-43-210-41-001000](#) [115-43-640-41-001000](#) [115-43-632-41-001000](#) [115-43-628-41-001000](#) [115-43-624-41-001000](#) [115-43-328-41-001000](#) [115-43-324-41-001000](#) [115-43-320-41-001000](#) [115-43-318-41-001000](#) [115-43-316-41-001000](#) [115-43-314-41-001000](#) [115-43-308-41-001000](#) [115-93-624-41-001000](#) [115-93-628-41-001000](#) [115-93-310-41-001000](#) [115-13-318-41-001000](#) [115-93-314-41-001000](#) [115-93-318-41-001000](#) [115-93-316-41-001000](#) [115-93-640-41-001000](#) [115-93-632-41-001000](#) [115-93-324-41-001000](#) [115-93-320-41-001000](#) [115-93-328-41-001000](#) [115-93-306-41-001000](#) [115-93-308-41-001000](#) [115-93-964-41-001000](#) [115-93-952-41-001000](#) [115-93-950-41-001000](#) [115-93-652-41-001000](#) [115-93-650-41-001000](#) [115-93-648-41-001000](#) [115-93-642-41-001000](#) [115-93-636-41-001000](#) [115-93-432-41-001000](#) [115-93-428-41-001000](#) [115-93-424-41-001000](#) [115-93-422-41-001000](#) [115-93-420-41-001000](#) [115-93-322-41-001000](#) [115-93-304-41-001000](#) [115-93-210-41-001000](#)