






Cross Section

Top Film	0.18 mm [0.007"]
Spacer	0.08 mm [0.003"]
Glass	2.36 mm [0.093"]
Panel Thickness	2.62 mm [0.103"]



Tail Connection

Strain Relief	0.13 mm [0.005"]
Tail	0.25 mm [0.010"]
Strain Relief	0.13 mm [0.005"]



Pin-Out

Pin 1:	Upper-Left
Pin 2:	Upper-Right
Pin 3:	Sense
Pin 4:	Lower-Right
Pin 5:	Lower-Left

Materials

Glass Backer:	ITO Coated Soda Lime Glass
Top Film:	Diffused
Connector:	AMP 487406-4 Pins AMP 487378-4 Housing
Tail:	Silver on Polyester

Tolerances

Sensor:	± 0.4 mm [0.015"] from datum corner
Tail Length:	± 2.5 mm [0.100"]
Total Panel Thickness:	±10%