



International Components Corporation
A reputation of excellence in the field of quality electronic components.

Product: **SURFACE MOUNT ELECTRO-ACOUSTIC TRANSDUCER**
Description: **ROHS COMPLIANT**
Part Number: **BST0503SM-03**


SPECIFICATIONS:

RATED VOLTAGE (VDC):	3.0 VDC
OPERATING VOLTAGE (VDC):	2.5 ~ 4.5
MAX CURRENT (mA)*:	120 mA
COIL RESISTANCE (OHMS):	10 B1 1.5
SPL OUTPUT (dB) MIN @ 10 CM*:	87dB min @
RESONANT FREQUENCY (Hz)*:	3100 Hz
OPERATING TEMPERATURE (°C):	-30 TO +70 B0C
FRAME DIAMETER (MM):	5.5 x 5.5 mm
FRAME DEPTH (MM):	2.5 B1 0.1 mm

COMMENTS:

*VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

DIMENSIONS:



International Components Corporation 215 McCormick Dr. Bohemia New York, 11716 . Tel: 800-645-9154 . E-mail: info@icc107.com . www.icc107.com