

List Price \$183.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Contacteur Type	Non-Reversing
Inductive Amperes (AC3)	Not Rated
Resistive Amperes (AC1)	32A
Certifications	UL Listed (E164862 / NLDX) - CSA Certified (LR43364 3211 04) - IEC Rated (60647-4) - CE Marked - RoHS Compliant
Horsepower Rating (3-Phase)	Not Rated
Marketing Trade Name	TeSys
Horsepower Rating (1-Phase)	Not Rated
Maximum Voltage Rating	600 Vac
Mounting Style	35mm DIN Rail
Number of Poles	4-Pole (4 NO)
Coil Voltage	24Vdc
Coil Voltage Code	BD
Terminal Type	Screw Clamp
Type	TeSys D

Shipping and Ordering

Category	22345 -
Discount Schedule	I12
GTIN	00785901503248
Package Quantity	1
Weight	1.4 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.