




3.000[76.2]	6	3.450[87.63]	3.900[99.06]	4.000[101.6]	266	5767094-7
2.500[63.5]	5	2.950[74.93]	3.400[86.36]	3.500[88.9]	228	5767094-6
2.000[50.8]	4	2.450[62.23]	2.900[73.66]	3.000[76.2]	190	5767094-5
1.500[38.1]	3	1.950[49.53]	2.400[60.96]	2.500[63.5]	152	5767094-4
1.000[25.4]	2	1.450[36.83]	1.900[48.26]	2.000[50.8]	114	5767094-3
.500[12.7]	1	.950[24.13]	1.400[35.56]	1.500[38.1]	76	5767094-2
.000[0]	0	.450[11.43]	.900[22.86]	1.000[25.4]	38	5767094-1
E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN G. ATTADIA 26 OCT 04 QWK D. DIXON 26 OCT 04 APVD D. DIXON 26 OCT 04		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: TOLERANCES UNLESS OTHERWISE SPECIFIED: INCHES		0 PLG ± - 1 PLG ± - 2 PLG ± - 3 PLG ± .005[0.13] 4 PLG ± - ANGLES ± - FINISH		NAME RECEPTACLE ASSEMBLY, .355[9.02] VERTICAL, .025[0.64] CENTER LINE, MICTOR	
		PRODUCT SPEC 108-1422 APPLICATION SPEC 114-11004		SIZE CAGE CODE DRAWING NO A1 00779 C=5767094	
MATERIAL 1 		WEIGHT 2 		RESTRICTED TO — CUSTOMER DRAWING SCALE 1:1 SHEET 1 OF 1 REV A	