



A selection of Master or Secondary (Slave/Extension) wall mounting sockets that are available with IDC or screw terminals. The sockets are either surface or flush mounted and are available in 3 different styles. The master sockets contain a 1.8μF capacitor, whilst the secondary sockets contain terminal connectors only.

Type 1 – Surface mount wall socket with all the components fastened to the cover. Supplied complete with wall fixing screws. Dims. (HxWxD): 67.5 x 67.5 x 29.1mm.

Type 2 – Flush mount wall socket with all the components fastened to the removable cover. Dims. (HxWxD): 84 x 84 x 21mm.

Type 3 – Flush mount wall socket with all the components fastened to the removable cover. The unit has two outlets from a single incoming line. Dims. (HxWxD): 84 x 84 x 21mm.

416021.409413

Description	BT Type	Order Code	Price Each
Type 1			
Master IDC	1/1A	133-5162	
Master Screw	1/4A	133-5163	
Extension IDC	1/3A	133-5164	
Extension Screw	LJV1/6A	133-5165	
Type 1			
Master IDC	2/1A	133-5343	
Master Screw	2/4A	133-5344	
Extension IDC	2/3A	133-5345	
Extension Screw	2/6A	133-5346	
Type 2			
Master IDC	3/1A	133-5347	
Master Screw	3/4A	133-5166	
Extension IDC	3/3A	133-5348	
Extension Screw	3/6A	133-5349	
Type 3			
Master IDC	4/1A	133-5350	
Extension IDC	4/3A	133-5351	
Extension Screw	4/6A	133-5353	
Extension Screw	5/1A	133-5354	
Master Screw	5/4A	133-5167	
Extension IDC	5/3A	133-5355	
Extension Screw	5/6A	133-5356	