

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

—

P

LTR

DESCRIPTION

DATE

DWN

APVD

E1

REVISED PER ECO-11-020548

12JAN12

KH

DR

AMP

INSULATION

SERRATIONS

BODY

WIRE STOP

28.58±0.89

[1.125±.035]

OBSOLETE

50

LOOSE PIECE BOX

INSULATION: PVC
COLOR: YELLOW
BODY: COPPER PER ASTM B152
ANNEALED
TIN PLATE PER ASTM B545

8-34205-2

500

LOOSE PIECE

34205

QTY

PACKAGE TYPE

MATERIAL & FINISH

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH —

MATERIAL —

FINISH —

DWN
KIRAN HOLAL
CHK
ROHDE DANIEL
APVD
ROHDE DANIEL
PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT —

12JAN12
12JAN12
12JAN12

STE

TE Connectivity

NAME
—
WIRE SPLICE PLASTI-GRIP-BUTT-OVALED
WIRE SIZE:12-10

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-34205

—

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV E1

1

FOR 7.14[.281] X 3.51[.138] MAX OVALED
WIRE INSULATION DIA

1470-19

(3/11)