

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-05-016219	24NOV05	JMS	FWK

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Ag PLATING
- 4 THIS ITEM MUST BE WHITE

- 5 HAND TOOL : 9-1478240-0
- 6 DIE SET : 9-1478242-0

- 7 ELECTRICAL CHARACTERISTICS
- FREQUENCY RANGE:

NOMINAL IMPEDANCE:

INSULATION RESISTANCE:

WORKING VOLTAGE:

DIELECTRIC WITHSTAND VOLTAGE:

CONTACT RESISTANCE:

CENTRE CONTACT:

OUTER CONTACT:

VSWR @ 2GHz:

INSERTION LOSS dB @ x 2 GHz:
- DC - 2 GHz

75 Ohm

5000 MOhm

500 Volts RMS at Sea Level

1500 Volts RMS Max

1.50 mOhm Max

0.20 mOhm Max

1.20:1 Max

0.20 Max

- 8 MECHANICAL CHARACTERISTICS
- COUPLING RETENTION FORCE:

CABLE RETENTION FORCE:

MOUNT NUT RECOMMENDED TORQUE:



DURABILITY:
- N/A

170N Min

4N

500 Cycles Min

- 9 ENVIRONMENTAL CHARACTERISTICS
- OPERATING TEMPERATURE:
- 65 to +165 DegC



		1	1	BRASS	3	CONTACT	8
		1	1	BRASS	3	FERRULE	7
		1	1	BRASS	3	CHASSIS	6
		1	1	PTFE		INSULATION	5
		1	1	BRASS	3	BODY	4
		1	1	SILICON RUBBER	4	GASKET	3
		1	1	STEEL	3	LOCKWASHER	2
		1	1	BRASS	3	HEX NUT	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM

QUANTITY PER ASSY				PARTS LIST			
-------------------	--	--	--	------------	--	--	--

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	24NOV05	tyco Tyco Electronics Corporation Electronics Bideford EX39 4HE		
		CHK	S.PARLOW	24NOV05			
DIMENSIONS: mm		APVD	F.WHEELER-KING	24NOV05	NAME BNC BULKHEAD JACK REAR MOUNT CRIMP 75 OHM RG59B/U, 62A/U, 140/U, 210/U, URM90, KX6A, KX25, KX52, KX53		
		PRODUCT SPEC	108-3435				
MATERIAL SEE TABLE		APPLICATION SPEC	411-3247		SIZE	CAGE CODE	DRAWING NO
		WEIGHT	-		A3	00779	C-1337436
		CUSTOMER DRAWING			SCALE	SHEET	REV
					NTS	1 OF 1	C