

DYMO®

Facility, Security, and Pro A/V

Rhino™ 4200

All-Purpose Labelling Tool with QWERTY Keyboard



Compact, time-saving labelling for on-the-go pros.

Get labelling jobs done fast – and done right.

The new DYMO® Rhino™ 4200 gets labelling jobs done fast – and done right. Easily navigate the familiar QWERTY keyboard. Use one-touch “Hot Key” shortcuts to quickly create and format wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-Length labels, breaker labels and more.

Print labels up to 19 mm wide in flexible nylon, permanent polyester and durable vinyl materials – PLUS print directly on heat-shrink tubes. Save even more time with great new features – like the ‘Favorites’ key which provides single-key access to commonly used labels, symbols and terms; and the ‘Custom’ key which eliminates repeated steps by saving customized settings.



DYMO® | Rhino™ 4200 features:

- 1 Easy to navigate computer-style QWERTY keyboard**
Quick and comfortable text entry
- 2 One-Touch “Hot Keys” – a DYMO® exclusive**
Shortcut keys for creating and formatting wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-Length, general and breaker labels
- 3 Industrial-strength labelling versatility**
Print 6 mm, 9 mm, 12 mm and 19 mm wide labels in a variety of materials and colours – PLUS print directly on heat-shrink tubes
- 4 NEW “Favorites” key**
Single-key access to your most commonly used labels, symbols and terms
- 5 NEW “Custom” key prevents needless repetition**
Customize and save settings for individual label formats



Rechargeable

Up to

**19
mm**



LABEL APPLICATIONS

LABEL COLOUR

6 mm

9 mm

12 mm

19 mm

24 mm

Labels that stick and stay stuck.

DYMO® Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO® Industrial labels have you covered. DYMO® Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces.

LEARN MORE: www.dymo.com/industrial

VINYL

- UL Recognized Component to UL969
- RoHS compliant



Length 5.5 m



BLACK ON WHITE

BLACK ON YELLOW

BLACK ON ORANGE

BLACK ON GREY

WHITE ON RED

WHITE ON BLACK

WHITE ON GREEN

WHITE ON BLUE

WHITE ON PURPLE


WHITE ON BROWN

PERMANENT POLYESTER

- UL Recognized Component to UL969
- RoHS compliant



Length 5.5 m



BLACK ON WHITE


BLACK ON CLEAR

BLACK ON METALLIC

HEAT SHRINK TUBES

- UL Recognized Component to UL224
- Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3)
- RoHS compliant

Length 1.5 m



BLACK ON WHITE


BLACK ON YELLOW

FLEXIBLE NYLON

- UL Recognized Component to UL969
- RoHS compliant



Length 3.5 m




BLACK ON WHITE

BLACK ON YELLOW

NON-ADHESIVE TAG

- RoHS compliant

Length 5.5 m



BLACK ON WHITE

SELF-LAMINATING

- RoHS compliant

Length 5.5 m



BLACK ON WHITE

Rhino™ 4200 SINGLE UNIT (BLISTER)

Code: S0955950

Box includes:

- Rhino™ 4200 printer
- Quick reference guide
- 12 mm white vinyl tape

Product specifications:

- Runs on optional rechargeable lithium-ion battery pack or 6 AA batteries
- 1 year warranty + 1 year extra when registering
- Unit weight: 770 gr

Optional accessories:

- AC adapter
- Rechargeable lithium-ion battery pack

Code: S0721430

Code: S0895840

For more information or to find out your nearest distributor, please visit www.dymo.com/industrial or call us at +44 (0) 20 7341 5529.



©2011 DYMO®
DYMO bvba, Industriepark-Noord 30
B9100 Sint-Niklaas, Belgium
www.dymo.com/industrial