








RECOMMENDED MOUNTING P.C.B LAYOUT





Copyright FCI.
FCI

	Title		DDR II 0.6mm PITCH 200 POS.	Rev.	
	Title		REVERSE TYPE ASS'Y	A	
	catalog no		-	CUSTOMER COPY	sheet 2 of 4
			10117865		



PRODUCT NO.

10117865-*52**



RECOMMENDED MODULE P.C.B LAYOUT

DETAIL Y
SCALE 10:1

Copyright FCI.
FCI



DDR II 0.6mm PITCH 200 POS.
REVERSE TYPE ASS'Y

10117865
CUSTOMER COPY
sheet 3 of 4

Rev.
A

PDM: Rev:A

STATUS: Released

Printed: Apr 22, 2011

Copyright FCI.

1	2	3	4	5	6	7	8
PRODUCT NO.	LOCATING PEG	TERMINAL CONTACT AREA FINISH	HOLD DOWN FINISH	SOLDER TAIL FINISH			
A	10117865-052FSLF	YES	Pure Sn PLATING	Au FLASH			
	10117865-152FSLF	NO					
	10117865-052TSLF	YES					
	10117865-152TSLF	NO					
	10117865-052ASLF	YES					
B	10117865-152ASLF	NO	Sn-Pb PLATING	Au FLASH			
	10117865-052FB	YES					
	10117865-152FB	NO					
	10117865-052TB	YES					
	10117865-152TB	NO					
C	10117865-052AB	YES	Pure Sn PLATING	Au FLASH			
	10117865-152AB	NO					
	10117865-252FSLF	YES					
	10117865-352FSLF	NO					
	10117865-252TSLF	YES					
D	10117865-352TSLF	NO	Sn-Pb PLATING	Pure Sn PLATING			
	10117865-252ASLF	YES					
	10117865-352ASLF	NO					
	10117865-252FB	YES					
	10117865-352FB	NO					
E	10117865-252TB	YES	Sn-Pb PLATING	Au FLASH			
	10117865-352TB	NO					
	10117865-252AB	YES					
	10117865-352AB	NO					
	10117865-452FS	YES					
F	10117865-552FS	NO	Pure Sn PLATING	Sn-Pb PLATING			
	10117865-452TS	YES					
	10117865-552TS	NO					
	10117865-452AS	YES					
	10117865-552AS	NO					
G	10117865-452FB	YES	Sn-Pb PLATING	Au FLASH			
	10117865-552FB	NO					
	10117865-452TB	YES					
	10117865-552TB	NO					
	10117865-452AB	YES					
H	10117865-552AB	NO	Sn-Pb PLATING	Au FLASH			

10117865- ☐ ☐ ☐ ☐ ☐ LF

For Rohs OPTIONS:
TAIL PLATING CODE MUST BE 0~3.
HOLD DOWN PLATING CODE MUST BE "S".
"LF" CODE IS EXIST IN THE END.
EX: 10117865-252TSLF

FOR NOT Rohs COMPATIBLE:
THIS "LF" CODE IS "BLANK".
EX:10117865-452TS

<PACKING METHOD>
R : TAPE REEL
DEFAULT : TRAY

<HOLD DOWN FINISH>
S : Pure Sn
B : Sn-Pb

<CONTACT AREA FINISH>
F : Au FLASH
T : Au 0.3μm MIN.
A : Au 0.76μm MIN.

<TOTAL HEIGHT>
52 : 5.2mm

<LOCATING PEG, SOLDER TAIL FINISH>
0 : YES, Au FLASH
1 : NO, Au FLASH
2 : YES, Pure Sn PLATING
3 : NO, Pure Sn PLATING
4 : YES, Sn-Pb PLATING
5 : NO, Sn-Pb PLATING

	DDR II 0.6mm PITCH 200 POS.	10117865	A
	REVERSE TYPE ASS'Y		
catalog no		CUSTOMER COPY	sheet 4 of 4