




HONEYWELL PART NUMBER
V15T16-CZ100A03-K
PRODUCT CODE
CFW2043

REV	DOCUMENT	CHANGED BY	CHECK
A	0038670	VS 10APR08	BLR



NOTES:
1. TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES
AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: MM			DRAWN	KSR	01APR08	Honeywell						
		CONTACT ARRANGEMENT		TOLERANCES UNLESS NOTED:			CHECK	RJ	01APR08							
OPERATING FORCE: 30gf MAX.		 16(4)A 250V~ 25T125 μ 5E4  16A 1/2HP 125/250VAC		NO PLACE X ± ±			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE						
DIFFERENTIAL FORCE:				ONE PLACE .X ± ±												
RELEASE FORCE: 5gf MIN.				TWO PLACE .XX ± ± 0.40			INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE B	TYPE I	CAGE CODE	DRAWING NAME V15T16-CZ100A03-K			REV A
FREE POSITION:				THREE PLACE .XXX ± ±												
OPERATING POSITION: 15.3±3MM.				ANGLES X ± ± 2°												
PRE-TRAVEL: 6.4MM MAX.		THIRD ANGLE PROJECTION			AutoCAD			SCALE	NTS				SHEET	1	OF	1
DIFFERENTIAL TRAVEL: 2.4MM MAX.																
OVER-TRAVEL: 2.6MM MIN.																
FULL OVERTRAVEL FORCE:																