


THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE. IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS



SPECIFICHE DI CARICO:

Componente spessore 4,0 mm forza F=20N min

Componente spessore 4,5 mm forza F=25N min

Componente spessore 5,0 mm forza F=30N min

CHARGE SPECIFICATIONS:

Thickness Component 4,0 mm force F=20N min:

Thickness Component 4,5 mm force F=25N min

Thickness Component 5,0 mm force F=30N min



**AAVID
THERMALLOY**
EUROPE www.aavidthermalloy.com

Via XXV Aprile, 82
40087 Cadriano - Bologna ITALY
Tel. +39 051 764011
Fax. +39 051 764028

COMPANY
WITH QUALITY SYSTEM
CERTIFIED BY DIN
ISO 9001

Cheney Manor
SWINDON WILTS SN1 8BN UK
Tel. +44 1793 401400
Fax +44 1793 810888

COMPANY
WITH QUALITY SYSTEM
CERTIFIED BY BSI
ISO 9002

Die n.	MATERIAL EN10132-4 C67S 0.35 x 4
Factor	GENERAL TOLERANCES
Part n.	
Area mm²	FINISH See note
Weight	
Note:	Zincatura bianca alta resistenza Zn high resistance plated Tratt. termico thermal treatment: BONIFICA 42-46 HRC all dimensions in mm
Drawn	S. Melotto
Check	

REV	Date	Revision description	By	SE	IF	Format	Scale	1
B	19Oct11	Confirm drawing				A4	1:1	
A	25Sep07	ORIGINAL (was ZA3899)						
REV	Date	Revision description	By	SE	IF	Format	Scale	1
						A4	1:1	

DRAWING n.
439647

Via n.
Description: 5901G Spring clip

