




UNIT: mm



PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 3 Ohm(max)
3. Insulation resistance: 20Mohm(min)
4. dielectric test: DC 300V

CNC Tech, LLC			Industrial Cable and Connector Technology		
DRAWN	Andy	DRAWING NO			
CHECKED		CUSTOMER			
APPROVAL		ITEM NO.		101-1010-BL-00500	
DECIDED		DATE		2013-8-23	
VERSIONS/EDITION		A/0	PROJECTION		
SPECIFICATION					
⑨	PE BAG	1/5	CLEAR SIZE: 360*380*0.05mm PRINT BLACK"MADE IN CHINA"+5PCS".		
⑧	PE BAG	1	CLEAR SIZE: 150*280*0.05mm PRINT BLACK"MADE IN CHINA".		
⑦	TIE	1	BLACK L=120mm		
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO: NM-027)		
⑤	OUT JACKET	7g	BLACK PVC-40P (MOULD NO: NM-83)		
④	OUT JACKET	6g	BLACK PVC-40P (MOULD NO: NM-40)		
③	CABLE	1	BLACK USB1.1 UI2725 28#/1P+24#/2C+AEB OD: 4.7mm L=5000 ± 20mm		
②	CONN	1	USB A FEMALE SHELL: NICKEL PIN G/F SHORT TYPE INSULATOR COLOR: WHITE		
①	CONN	1set	USB A MALE SHELL: NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE		
NO.	NAME	Q'TY			

4

3

2

1