

APPLICATOR PARTS LIST

TYPE

END FEED

(PIGTAIL)
SPLICEAMP INCORPORATED
HARRISBURG, PENNA.

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA	TERMINALS
1	■ WIRE CRIMPER	1	4564093	42				TO APPLY TERMINAL	60932
2	■ INS. CRIMPER			43				SPEC 114-2088	62776
3	■ ANVIL	1	465274-5	44	HOLD DOWN	1	810640-1	WIRE SIZE	
4	ANVIL SPACER			45	SPACER	2	375310	CRIMP HEIGHT	
5	■ SHEAR BLADE, 070 TMR.	1	472517-3	46	CLEANER	1	389114		
6	■ REAR SHEAR PLATE	1	385013-4	47					
7	SHEAR BLADE SPACER	2	370709	48					
8	■ FRONT SHEAR PLATE			49					
9	REAR ANVIL SPACER PLT.			50				CRIMP	
10	FRONT ANVIL SPACER PLT.			51				SIZE	
11	TOOL SPACER	1	374180	52				TYPE	
12	CRIMP SPACER			53				FEED	
13	FRONT STRIP GUIDE	1	371638	54				WIRE	.120
14	REAR STRIP GUIDE	1	371638	55				INSUL.	
				56				SLEEVED	.214
15	RAM	1	471911	57				WIRE RANGE	
16	TOOL HOLDER			58				CMA 2048-4217	
17	ADJ. CRIMP MOUNT			59				EXPLODED VIEW	
18	ADJ. BLOCK			60				A-6000 A-6000-13	
19	APPLICATOR MOUNT ASSY.	1	570656	61				REMARKS:	
20	BASE PLATE			62				① MOUNT LOW	
21	BASE BLOCK			63				② MOUNT HIGH	
22	STRIP GUIDE PLATE			64				BETWEEN 26 & 45	
23	ANVIL HOLDER			65	TENSION ADJ. PLATE	1	374999		
24	AUX. ANVIL HOLDER				MISCELLANEOUS				
25	STRIPPER	1	388671	66	LUBRICATOR ASSY.	1	465184-2		
26	STRIPPER MOUNT	2	379613	67	TERMINAL LUBRICANT	REF	852931-2		
27	RETAINER PLATE	2	372251	68					
28	STRIPPER MOUNT BRACKET			69					
29	STRIPPER BUSHING			70	COPPER TUBE	1	689446-2		
30	STOCK DRAG	1	376666	71	ELBOW	1	22317-3		
31	STOCK DRAG HANDLE			72	AIR BLAST ASSY.	1	455350-2		
32	STOCK DRAG STUD	2	354045-1	REV.	REVISION RECORD	DATE	BY	ECN	
33	STOCK DRAG SPRING	2	1-23847-1	01	ADDED 62776 PER ECN	5-19-78	BU	R-2518	
34	STOCK DRAG ADJ. SCREW	2	372997	A	ECN A-272490	10-16-90	JED	CE	
35	FEED FINGER HOLDER			B	ECN A-395892	9-92	MD	TE	
36	FEED FINGER	1	452817-1	B1	ECN 0150-1194-04	9-04	MY	TE	
37	FEED FINGER TIP								
38	FEED FINGER SPACER								
39	BASE CASTING	1	570238						
40	GUARD	1	457664-7						
41									

TO APPLY TERMINAL

SPEC 114-2088

WIRE SIZE

CRIMP HEIGHT

CRIMP

SIZE

TYPE

FEED

WIRE

.120

F

INSUL.

.214

SLEEVED

WIRE RANGE

CMA 2048-4217

EXPLODED VIEW

A-6000 A-6000-13

REMARKS:

① MOUNT LOW

② MOUNT HIGH

BETWEEN 26 & 45

■ DENOTES WEARING PARTS
RECOMMEND PURCHASE REPLACEMENT

THIS APPLICATOR IS TO BE USED ON

AMP-O-LECTRIC 1-471273-3

AMP-O-LECTRIC MECH. FEED

ALIGN GA. 679597-1

SERIAL NO.

DATE SHIPPED

CUSTOMER NAME AND ADDRESS

THIS DRAWING IS A CONTROLLED DOCUMENT.

APPLICATOR
NUMBER

REV.

B1 566267-1

SHEET

1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566267-1](#)