



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISI



| REV | DESCRIPTION | DATE | CHANGED BY |
|-----|-----------------------------|----------|------------|
| A | RELEASED FOR PRODUCTION | 05/10/01 | MCCORMICK |
| B | ECN 3112: UPDATE DWG FORMAT | 12/14/07 | D.GRIFFIN |
| | | | |



2X BNC JACK
(50 OHM IMPEDANCE)



RECOMMENDED
PANEL OPENING



LOCKWASHER



5/8 HEX NUT

NOTES:

MATERIAL:

BODY - NICKEL PLATED PHOSPHOR BRONZE
CENTER CONTACT - BRASS
INSULATION - DELRIN

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

TOLERANCES TO BE:
.X ±.1 [2.5]
.XX ±.01 [.25]
.XXX ±.005 [.13]
ANGLES ±2°

OVERALL CABLE LENGTH TOL:
≤ 60 [1524] +3 [76.2] / -0
> 60 [1524] +5% / -0%

PROJ

APPROVALS

DRAWN BY
MCCORMICK
05/01/01

CHECKED BY

D.PARHAM
05/10/01

APPROVED BY

R.CARRICK
05/10/01

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com
CONNECTIVITY
PRODUCTS

45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

CATEGORY

COAXIAL

PRODUCT DESCRIPTION

BNC CONNECTORS AND ADAPTORS

SIZE

A
43321

FCM NO.

BA1087

DWG. NO.

BA1087

REV.

B

SCALE: NONE

CAD FILE: BA1087.SLDDRW

SHEET 1 OF 1