



Home > 4-4 FBZ-SS-C > 4-4 HBZ-SS-C > 4-4 T2HG-SS > 4-4 WBZ-SS-C > 4FBT4N-B > 4KBZ-SS-C > 6-2 MHN-B > 62PLP-4 > 66C-4-4 > 6-6 EBZ-SS-C > 68P-5-2 > 68P-5-4 > 68PLP-4-0 > 6BF6-B > 6BZ-SS-C > 6FF6-B > 6FSC4N-B > 6NU6-B > 8311AMVS60 > 8-8 FHC-B > B22 > N4UC4 > N8MC8 > NI219P-2 > P4MEB4 > W169PLP-4-2 > W169PLP-4-4 > W169PLP-6-4 > W172PLP-6-4 > W68PLP-6-4

W68PLP-6-4



DESCRIPTION	ATTRIBUTE VALUE
PRODUCT TYPE	LOW PRESSURE FITTING STRAIGHT, TUBE TO PIPE
TUBE SIZE	0.375
TUBE CONNECTION	Push to Connect
PIPE SIZE	0.25
PIPE CONNECTION	NPTF
MATERIAL	NICKEL PLATED BRASS
ADDITIONAL DETAIL	N/A
TRADE/BRAND NAME	PRESTOLOK PLUS
SYNONYM	n/a

Where to Buy
Contact Us

View All Parts

Download 3D Model
STP