

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
HM	00	P	LTR	DESCRIPTION	DATE	APVD
		A		REV ECR-09-024322	30OCT09	LH JS

PART NUMBER	L (METER)	L (FEET)	MT-RJ(No Pins)		Right Side –	
			Black	No Connector	IL(dB)	RL(dB)
0-1907884-1	0.950 – 1.050	3.11 – 3.44	IL(dB)	RL(dB)	IL(dB)	RL(dB)
			0.5	20	–	–



1. CABLE ASSEMBLY TESTED AT 1300NM.
2. TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
3. CABLE INFO:

– CORE DIAMETER: 50µm

– OUTER JACKET DIAMETER: 2,8mm

– OUTER JACKET COLOUR: AQUA

– OUTER JACKET MATERIAL: OFNP



SECTION X-X
SCALE 4:1

MT-RJ	FIBRE COLOUR
A	ORANGE/NATURAL
B	BLUE

1	TRACE LABEL	3
1	MTRJ CONNECTOR, FEMALE SECURE, MULTI MODE, RED	2
L	DUALAN XG 50/125 JACKETED CABLE, AQUA	1
QTY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

METERS

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN G. GARRETT 23SEP2009

CHK J. SHIPE 23SEP2009

APVD J. SHIPE 23SEP2009

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
's-Hertogenbosch, Nederland

NAME FOMM50 PIGTAIL DUALAN / T / SECURE
MT-RJ FEMALE RED

SIZE A2 CAGE CODE 00779 DRAWING NO C=1907884 RESTRICTED TO -

SCALE NTS SHEET 1 OF 1 REV A