


SPECIFICATION FOR APPROVAL

TO:


2/1

PART NAME	EMI FILTER		
YUNPEN MODEL	YB10A1-B	SAMPLE DATE	AUG.04.2008
USED NO		OUR DRAWING NO	YDR-00377


1. PHYSICAL DIMENSIONS:(mm)



SUGGESTED CUTOUT
MOUNTING DIMENSIONS
OF SOCKET



2. SCHEMATIC:



CX : 0.1uF
CY : 3300pF ± 20%
L : 2 x 0.3mH

REPORTED BY	CHECKED BY	APPROVED BY	3	
工程部部长 王继军 080805	王继军 080805	王继军 080805	2	
			REV. 1	

CK002 30101

SPECIFICATION FOR APPROVAL

TO:

2/2

PART NAME	EMI FILTER		
YUNPEN MODEL	YB10A1-B	SAMPLE DATE	AUG.04.2008
USED NO		OUR DRAWING NO	YDR-00377

3.ELECTRICAL CHARACTERISTICS:

3-1.RATED VOLTAGE	125/250VAC
3-2.RATED CURRENT	10 A
3-3.OPERATING FREQUENCY	50/60Hz
3-4.LEAK CURRENT:EACH LINE TO GROUND 250VAC 50Hz	0.8mA MAX
3-5.HIPOT RATING:(FOR ONE MINUTE) LINE TO LINE	1450VDC
LINE TO GROUND	1800VAC
3-6.INSULATION RESISTANCE	250VDC/100MOHM MIN
3-7.DIRECT CURRENT RESISTANCE	0.1 OHM MAX
3-8.OPERATING TEMPERATURE	-25 TO +85°C

4.SAFETY COMPLIANCE:

UL FILE NO:E134751
CSA FILE NO:LR95210
VDE FILE NO:40007880
CE

REPORTED BY	CHECKED BY	APPROVED BY	3	
97.8.5 王統賢	陳銘	張平	2	
			REV. 1	

CK002 30101